

Metal Table Screens

Now Open for Orders
3-4 Week Lead Time




Allsteel universal metal table-mounted screens offer a cleanable, easily retrofitted solution to create boundaries within the workplace. Available in 20"H and 25"H, metal screens offer users a sense of privacy while also providing a magnetic surface for posting notes or an optional marker board finish as a writable surface. Extended lateral screens offer an additional 12" boundary between users.

Description	SPLA Model
Mtl Table Screen, 20"H x 45½"W (for 48"W)	ASIMTLSCRN2048
Mtl Table Screen, 20"H x 51½"W (for 54"W)	ASIMTLSCRN2054
Mtl Table Screen, 20"H x 57½"W (for 60"W)	ASIMTLSCRN2060
Mtl Table Screen, 20"H x 63½"W (for 66"W)	ASIMTLSCRN2066
Mtl Table Screen, 25"H x 45½"W (for 48"W)	ASIMTLSCRN2548
Mtl Table Screen, 25"H x 51½"W (for 54"W)	ASIMTLSCRN2554
Mtl Table Screen, 25"H x 57½"W (for 60"W)	ASIMTLSCRN2560
Mtl Lat Screen 20"H x 21"D (for 24"D)	ASIMTLSCRN2024
Mtl Lat Screen 20"H x 25"D (for 27"-30"D)	ASIMTLSCRN2030
Mtl Lat Screen 20"H x 34"D (for 36"D)	ASIMTLSCRN2036
Mtl Lat Screen 25"H x 21"D (for 24"D)	ASIMTLSCRN2524
Mtl Lat Screen 25"H x 25"D (for 30"D)	ASIMTLSCRN2530
Mtl Lat Screen 25"H x 34"D (for 36"D)	ASIMTLSCRN2536
Mtl Extended Screen 20"H x 33¾"D (for 24"D)	ASIMTLEXSCRN2036
Mtl Extended Screen 20"H x 37¾"D (for 30"D)	ASIMTLEXSCRN2042
Mtl Extended Screen 25"H x 33¾"D (for 24"D)	ASIMTLEXSCRN2536
Mtl Extended Screen 25"H x 37"D (for 30"D)	ASIMTLEXSCRN2542

- Screens are offered as extended lateral (for 24" or 30"D worksurfaces), lateral (for 24", 30", or 36"D surfaces), or table-mounted configurations (for 48" through 66"W worksurfaces).
- Screen depths are undersized to accommodate Further™ or Altitude® worksurface depths but can also be added to panel systems or tables products.
- Brackets attach to the top of the worksurface using an industrial grade adhesive. Installation does not require any drilling or defacing of the worksurface. Screens and brackets may be removed in the future, if desired.
- The front of the bracket has a beveled zinc cap, and the back of the bracket has exposed hardware. Brackets are non-handed so that the front and back can be oriented either direction, based on the application.
- Screens meet or exceed ANSI/BIFMA X5.5-2014 Sections 4.6 and 9.

Offered in 32 standard Allsteel powder-coat paint finishes, including a marker board finish. P2 is \$20 upcharge, P3 is \$40 upcharge, P6 (marker board) is a \$100 upcharge. Bracket will match the finish of the screen.



Acrylic Table Screens

Now Open for Orders
3-4 Week Lead Time




Allsteel universal acrylic table mounted screens offer a cleanable, easily retrofitted solution to create boundaries within the workplace. Available in 20"H and 25"H, acrylic screens offer users protection and personal division within a workspace. Extended lateral screens offer an additional 12" boundary between users.

Description	SPLA Model
Acry Table Screen, 20"H x 45 1/2"W (for 48"W)	ASIACRYSCRN2048
Acry Table Screen, 20"H x 51 1/2"W (for 54"W)	ASIACRYSCRN2054
Acry Table Screen, 20"H x 57 1/2"W (for 60"W)	ASIACRYSCRN2060
Acry Table Screen, 20"H x 63 1/2"W (for 66"W)	ASIACRYSCRN2066
Acry Table Screen, 25"H x 45 1/2"W (for 48"W)	ASIACRYSCRN2548
Acry Table Screen, 25"H x 51 1/2"W (for 54"W)	ASIACRYSCRN2554
Acry Table Screen, 25"H x 57 1/2"W (for 60"W)	ASIACRYSCRN2560
Acry Table Screen, 25"H x 63 1/2"W (for 66"W)	ASIACRYSCRN2566
Acry Lat Screen 20"H x 21"D (for 24"D)	ASIACRYSCRN2024
Acry Lat Screen 20"H x 25"D (for 30"D)	ASIACRYSCRN2030
Acry Lat Screen 20"H x 34"D (for 36"D)	ASIACRYSCRN2036
Acry Lat Screen 25"H x 21"D (for 24"D)	ASIACRYSCRN2524
Acry Lat Screen 25"H x 25"D (for 30"D)	ASIACRYSCRN2530
Acry Lat Screen 25"H x 34"D (for 36"D)	ASIACRYSCRN2536
Acry Extended Screen 20"H x 33 3/8"D (for 24"D)	ASIACRYEXSCRN2036
Acry Extended Screen 20"H x 33 3/8"D (for 24"D)	ASIACRYEXSCRN2042
Acry Extended Screen 20"H x 37"D (for 30"D)	ASIACRYEXSCRN2536
Acry Extended Screen 25"H x 37"D (for 30"D)	ASIACRYEXSCRN2542

- Screens are offered as extended lateral (for 24" or 30"D worksurfaces), lateral (for 24", 30", or 36"D surfaces), or table-mounted configurations (for 48" through 66"W worksurfaces).
- Screen depths are undersized to accommodate Further™ or Altitude® worksurface depths but can also be added to panel systems or tables products.
- Brackets attach to the top of the worksurface using an industrial grade adhesive. Installation does not require any drilling or defacing of the worksurface. Screens and brackets may be removed in the future, if desired.
- The front of the bracket has a beveled zinc cap, and the back of the bracket has exposed hardware. Brackets are non-handed so that the front and back can be oriented either direction, based on the application.
- Screens are made of 0.170" thick high-impact clear acrylic.
- Screens meet or exceed ANSI/BIFMA X5.5-2014 Sections 4.6 and 9.

Bracket color must be specified. Available in Allsteel Standard Paints. P2 is \$10 upcharge, P3 is \$15 upcharge.



Acrylic Freestanding Screens

Now Open for Orders
3-4 Week Lead Time



Acrylic Freestanding Screens offer a cleanable, transparent solution to create a protective barrier between users. Models with a transaction cut-out are a solution for reception and other front-desk applications. Varying screen sizes provide solutions for different types of spaces. From a large reception desk to a smaller check-in space, this screen solution blocks germs without interrupting communication.

- Screens are supported by two black feet. Feet are only available in a black finish.
- Feet dimensions are 12"H x 10⁵/₈"W.
- Screens are offered as a freestanding solution and do not adhere or mount to a worksurface or tabletop.
- Transaction cut-out screens stand 36"H and are offered in 30", 36", and 48"W.
- Freestanding screen without a cut-out is available in 24" or 30"H and 30", 36", or 48"W.
- Screens are made of 0.220" thick high-impact clear acrylic.



Description	SPLA Model
Acry Freestanding Screen Cutout 36"H x 30"W	ASIACRYFSSCRNC3630
Acry Freestanding Screen Cutout 36"H x 36"W	ASIACRYFSSCRNC3636
Acry Freestanding Screen Cutout 36"H x 48"W	ASIACRYFSSCRNC3648
Acry Freestanding Screen 24"H x 30"W	ASIACRYFSSCRNX2430
Acry Freestanding Screen 24"H x 36"W	ASIACRYFSSCRNX2436
Acry Freestanding Screen 24"H x 48"W	ASIACRYFSSCRNX2448
Acry Freestanding Screen 36"H x 30"W	ASIACRYFSSCRNX3630
Acry Freestanding Screen 36"H x 36"W	ASIACRYFSSCRNX3630
Acry Freestanding Screen 36"H x 48"W	ASIACRYFSSCRNX3648


Hands-Free Pulls

Now Open for Orders
3-4 Week Lead Time




Allsteel foot and arm pulls allow for hands-free entry on any latch-less door. A hands-free operation helps to prevent cross-contamination in high traffic areas. The hands-free pulls are shipped with mounting hardware to accommodate either metal or solid wood doors and are offered in either a pack of 5 or 15.

- Hands-free pulls are ideal for high-traffic areas.
- Hands-free pulls can be installed in minutes using the included mounting hardware.
- Toothed edge on foot pull ensures a no-slip grip.
- Offered in Textured Titanium (P8V) and Textured Black (P6P).



Arm Pull
7 3/8" H x 2 1/2" W x 4 1/2" D



Foot Pull
1 5/8" H x 5" W x 3 1/4" D


Description	SPLA Model
Allsteel Door Foot Pull 5 PACK	ASIFOOTPULL5
Allsteel Door Foot Pull 15 PACK	ASIFOOTPULL15
Allsteel Hands Free Door Arm Pull 5 PACK	ASIARMPULL5
Allsteel Hands Free Door Arm Pull 15 PACK	ASIARMPULL15

Height-Adjustable Table Foot Control

Now Open for Orders
3-4 Week Lead Time

The Allsteel height-adjustable table foot control allows for hands-free adjustment at any Altitude® A6 or A3 table. Hands-free operation helps prevent the spread of germs, making this control a great solution for individual or shared workspaces.

- Compatible with the existing Altitude A3 and the new Altitude A6 height-adjustable tables.
- Available in grey only.
- Wireless design offers clean and functional solution.
- Can be paired with a standard control pad for dual control function.
- Easy to install instructions for retrofitting current workstations or adding on to new Altitude A6 workstations.
- Requires 2 AAA batteries. Batteries not included.



1½" x 7½" W x 4½" D

Description	SPLA Model
A3/A6 Wireless Foot Control Pad	A6FOOTCNTL


Hand Sanitizer Solutions

Now Open for Orders
3-4 Week Lead Time



Allsteel offers an easy and accessible sanitizing solution, helping employees stay bacteria-free while moving throughout the office. Incorporating freestanding stations within the facility aids in preventing the transfer of germs between meetings and high-traffic areas. Bottle holders at individual workstations free up valuable workspace to allow for easy surface cleaning while promoting more frequent sanitizing.

- Ideal for high-traffic areas and workstations.
- Available freestanding on base and mounted to panel wall or tool rail and tile.
- Metal freestanding base for added stability. Drip tray prevents sanitizer spills.
- Holder is compatible with most standard hand sanitizer dispensers.
- Easy installation: holder for panel or tool rail and tile can be attached through the pre-drilled holes or via double-sided tape. Additional mounting holes can be drilled to fit a non-standard dispenser.
- Velcro attachment can be used to hold other disinfectants.
- Hand sanitizer dispenser sold separately.



Description	SPLA Model
Freestanding Hand Sanitizer Stand with Drip Tray	ASISANSTND
Panel Mount / Wall Mount Hand Sanitizer Bottle Holder	SPLA-HC-ACCYHRDWPM505015.PAINT
Tool Tile / Tool Rail Mounted Hand Sanitizer Bottle Holder	SPLA-HC-ACCYHRDWPM505017.PAINT

Offered in 32 standard Allsteel powder-coat paint finishes. P2 is \$13 upcharge; P3 is \$22 upcharge.

Wall Mounted Sanitizer Holder

Now Open for Orders
3-4 Week Lead Time


Having a place to hold hand sanitizers either on panels or architectural walls, keeps items in consistent locations and prevents cluttering a table or worksurface. The hand sanitizer holder can be inserted into Beyond's slotted standards between panels. The holder is designed to fit most 8 oz bottles of hand sanitizer.

This model contains the following parts: a left-hand and a right-hand bracket that fit into Beyond's 5/8" slotted standards, a metal holder that screws into the bracket, and a hardware pack with 4 screws. Only one bracket is needed for installation and the holder can be positioned in a right, left or centered location.

- The metal mount can be finished in any Beyond or Aspect standard painted metal finishes. It will be painted in an anodized-like silver powder coat if anodized clear is selected.
- To attach the mount to Aspect, no bracket is needed. Simply screw the bracket into Aspect between the door jamb and panel vertical.
- If mounting into a panel system, a different bracket is needed to work with furniture's 1/2" slotted standards (see Hand Sanitizer Solutions).
- The mount can also be screwed into drywall with no bracket needed.



Metal Holder



Beyond Bracket

Description	SPLA Model
Hand Sanitizer Holder – Clear Anodized*	SPLW-SANITIZER.M505403.AALCLR
Hand Sanitizer Holder – Painted	SPLW-SANITIZER.M505403.PNT_ _ **

*Note: Holder will be painted in a light silver powder coat to match anodized.

**Choose from 30 Beyond and Aspect standard painted metal options. See Beyond and Aspect specification guides for full listing of finishes.

4-5 week lead time when ordered with Aspect finishes. 6-8 week lead time when ordered with Beyond finishes.

Altitude® A8 Screens Now Available in Contourett

A Durable & Easy-to-Clean Polyurethane
Now Open for Orders



Altitude A8 screens create a natural privacy barrier above and below the worksurface. The A8 screen extends 21¾" above and 10" below the worksurface, creating a boundary around your personal workspace in a clean and attractive way. As workspace design evolves, creating a sense of physical privacy and personal space can help promote individual well-being. Adding a privacy screen, like an A8 screen, to compatible work surfaces offers the much-needed personal perimeter we now look for in our workspace.


A8 screen kits (U, Rectangle) are now available in Contourett, a non-tackable 100% polyurethane, a durable and easy-to-clean surface that allows for the use of a variety of cleaning agents.

[Material Cleaning Resources →](#)

Statement of Line



48" 54" 60" 66" 72"
Rectangle Screen Kit



48" 54" 60" 66" 72"
U Screen Kit

Available to order as a Standard Special in Contourett colors



Size / Shape	SPLA Model
48" U	SPLA-A8-FABSCRNPNTA.M505257.FABRIC.PAINT
54" U	SPLA-A8-FABSCRNPNTA.M505258.FABRIC.PAINT
60" U	SPLA-A8-FABSCRNPNTB.M505259.FABRIC.PAINT
66" U	SPLA-A8-FABSCRNPNTB.M505260.FABRIC.PAINT
72" U	SPLA-A8-FABSCRNPNTB.M505261.FABRIC.PAINT
48" Rectangle	SPLA-A8-FABSCRNPNTA.M505262.FABRIC.PAINT
54" Rectangle	SPLA-A8-FABSCRNPNTA.M505263.FABRIC.PAINT
60" Rectangle	SPLA-A8-FABSCRNPNTB.M505264.FABRIC.PAINT
66" Rectangle	SPLA-A8-FABSCRNPNTB.M505265.FABRIC.PAINT
72" Rectangle	SPLA-A8-FABSCRNPNTB.M505266.FABRIC.PAINT




Specifying for Freestanding Worksurfaces

Altitude A8 screens are designed to fit on Altitude worksurfaces, which are undersized by 2" to allow for height-adjustable motion. This is a common design for height-adjustable worksurfaces, but there are a few steps to take to verify non-Altitude worksurfaces are compatible.

1. Understand measurements of worksurface
2. Match with correct A8 screen size
3. Consider clearance of modesty screen and mounting brackets

Example: 48" Altitude Worksurface (AF5RS4824) is actually 46". A 48" U-Screen kit would be the correct screen size to specify with this worksurface.

Allsteel Customer Support is available to verify when needed.



How to Clean

Contourett

- For wet spills, gently blot with dry cloth to remove spill.
- For dried spills, gently work the spill in a non-aggressive circular motion using a damp cloth, making sure to not oversaturate the fabric.
- For dried stains, use a mixture of Tide or Oxiclean and warm water (1 teaspoon of soap for every 16 ounces of water). Follow instructions for dried spills above. Make sure to wipe away any excess soap left behind and remove any moisture with a dry cloth.
- For non-liquid spills, always remove excess contaminant from surface before cleaning. The use of a soft brush or soft abrasive can be used to remove dried contaminants before performing liquid cleaning.
- For healthcare related stains, a water-to-bleach solution of 5:1 is recommended. Rinse cleaned area with water.
- For stains requiring the use of a solvent, spray the solvent directly onto the stain and allow it to sit for 2-3 minutes, avoiding over saturating the fabric. Follow directions for dried stains above.
- Always allow fabric to air dry.

Approved Cleaners for Contourett

It is important to remember that after use of any cleaning agent, the fabric should be rinsed with water and wiped dry to remove any remaining residue or moisture. Approved cleaning agents include Shockwave, Recon, Benefect, Microban, Greased Lightning Degreaser, Lysol Wipes, Diluted bleach solution (5:1 water to bleach), Dispatch Disinfectant Towels with bleach, PDI Sani-Hands Wipes, PDI Super Sani-Cloth Germicidal Disposable Wipes, Diversity Morning Mist Neutral Disinfectant Cleaner, Virex 256, Fantastik, Oxycide, Formula 409.